




HEATH & SHERWOOD

rotary vezin sampler

Model 4710-3500

Accurate Sampling of Slurry or Dry Solids from Rotary Action Cutter following the Recommendations of Existing Standards and Consultants

Continuous or optional intermittent sample splitting from an easy to install self-contained module




rotary vezin sampler

Model 4710-3500



major components (standard design- two cutter slurry version)



- | | | |
|--|--|--|
| <p>1 top mounted access doors</p> <p>2 standard motor for continuous operation:
1/4 hp T.E.F.C. at customer required voltage</p> <ul style="list-style-type: none"> standard motor for intermittent operation or for waterflush option: 1/3 hp T.E.N.V. brakemotor at customer required voltage. Premium efficiency motors (IEEE-841, 1 hp) available on request. <p>3 cutter cap available in molded polyurethane, stainless, or abrasion resistant steel</p> | <p>4 cutter(s) available in arrangements of 1 to 4 sets</p> <p>5 body constructed of heavy steel plate (stainless steel available on request)</p> <p>6 2, 2 1/2 or 3 inch inlet connection, victaulic or flange</p> <p>7 3 inch pipe outlet, victaulic or flanged</p> <p>8 water spray nozzles to clean cutters in parked position (optional)</p> | <p>9 side mounted access doors</p> <p>10 transition bottom (as shown) also available in open bottom</p> <p>11 4 inch process connection (victaulic, flange or custom)</p> <ul style="list-style-type: none"> weight: 639 lbs (291 kg) intermittent operation also available dry solids version available CE marking available |
|--|--|--|

Heath & Sherwood (1964) Limited
Box 340 Kirkland Lake, Ontario
Canada P2N 3J2

Tel. (705) 567-5313
Fax. (705) 568-8545
Toll Free in North America:
1 888-go sample (467-2675)
email: info@heathandsherwood64.com

Subsidiary Offices:
Toronto, Ontario Canada
Agents World Wide

Visit our website at:
www.heathandsherwood64.com