




HEATH & SHERWOOD

rotary vezin sampler

Model 4720

Accurate Sampling of Slurry or Dry Solids from Rotary Action Cutter following the Recommendations of Existing Standards and Consultants

Continuous or optional intermittent sample splitting from an easy to install self-contained module




rotary vezin sampler

Model 4720



major components (standard design- two cutter slurry version)



- | | | |
|--|--|--|
| <p>1 top mounted access doors</p> <p>2 standard motor 1/3 hp NEMA 56C frame for continuous duty or brakemotor for intermittent duty
 ■ optional motor: 1hp IEEE-841 NEMA 143TC frame for continuous duty or brake motor for intermittent duty</p> <p>3 replaceable cutter blades
 ■ available in UHMW polymer, stainless steel or abrasion resistant steel</p> <p>4 cutter(s) available in arrangements of 1 to 4 sets</p> | <p>5 body constructed of heavy steel plate (stainless steel available on request)</p> <p>6 4 or 6 inch inlet with either flange or victaulic groove connection</p> <p>7 6 or 8 inch pipe outlet with either flange, victaulic or custom connection</p> <p>8 water spray nozzles to clean cutters in parked position (optional)</p> | <p>9 side mounted access door</p> <p>10 transition bottom (as shown) also available in open bottom</p> <p>11 3 inch sample outlet with either flange, victaulic, or custom connection
 ■ weight: 700# 327 kg (model with single cutter and standard motor)
 ■ intermittent operation also available
 ■ CE marking available</p> |
|--|--|--|

Heath & Sherwood (1964) Limited
 Box 340 Kirkland Lake, Ontario
 Canada P2N 3J2

Tel: (705) 567-5313
Fax: (705) 567- 8545
Toll Free in North America:
 1 888-go sample (467-2675)
email: info@heathandsherwood.com

Subsidiary Offices:
 Mississauga, Ontario Canada
 Agents World Wide

Visit our website:
www.heathandsherwood.com